



Täydellinen tekninen dokumentaatio

PlastShop.se

POM C FG 200/160x3000 mm liikenne sininen

Tuotenro P1007732

1. Tekninen tietolomake

Ominaisuus	Arvo	Yksikkö	Testausstandardi
Tiheys	1.24	g/cm ³	ASTM D792
Imeytymisen maksimointi	2.2	%	ASTM D955
Vesihaku kyllästymiseen	0.5	%	ASTM D570
Venymisrajan jännitys	51	MPa	DIN EN ISO 527-2
Joustavuusmoduli (vetolujuus)	1200	MPa	ASTM D790
Murtolujuus	76.5	MPa	ISO 527
Murtovenymä	300	%	ASTM D638
Taivutuslujuus	58	MPa	ASTM D638
Särkyäkesto (Charpy)	6	kJ/m ²	DIN EN ISO 179-1
Iskunkestävyys (Charpy)	19	kJ/m ²	ISO 179/1eU
Kovuus Shore D	83	° Shore D	ISO 868
Kulmapaineen kovuus	230	MPa	ISO 2039-1
Sulamispiste	222	°C	ISO 3146
Maksimaalinen käyttölämpötila (lyhytaikainen)	129	°C	UL746B
Maksimi käyttölämpötila	90	°C	
Alin lämpötila	-46.25	°C	
Lämpökäyrä (HDT/A)	105	°C	ASTM D648
Lämpökäyrä (HDT/B)	155	°C	ISO 75
Vicat-pehmenemislämpötila (VST/B/50)	50	°C	ISO 306
Lämmönjohtavuus	0.3	W/(m·K)	DIN 52612
Lämpölaajenemiskerroin	0.4	10 ⁻⁴ /K	ISO 11359
Dielektrinen voimakkuus	85	kV/mm	IEC 60243-1
Tilavuusresistanssi	10 ¹²	Ω	IEC 60093
Dielektrinen vakio (1 MHz)	3.7	-	IEC 60250
Dielektrinen hajoamiskerroin (1 MHz)	0.0	-	IEC 60250

Kemikaali	Pitoisuus	Kestäv.
Ethyl alcohol (ethanol)	96%	●
Food oil	—	●
Formaldehyde, aqueous	40%	●
Formic acid	10%	●
Frost protection agent	—	●
Fuel oil	—	●
Fuel, aromatic free	—	●
Glycerine	100%	●
Glycol	100%	●
Heptane	100%	●
Hydrochloric acid	10%	●
Hydrochloric acid (concentrated)	conc.	●
Hydrofluoric acid	40%	●
Hydrogen peroxide	10%	●
Hydrogen sulfide, aqueous	—	●
Isopropyl alcohol	100%	●
Linseed oil	—	●
Mercurochrome	—	●
Methyl alcohol (methanol)	100%	●
Methyl ethyl ketone (MEK)	100%	●
Methylene chloride	100%	●
Milk	—	●
Mineral oils (aromatic free)	—	●
Nitric acid	10%	●
Nitric acid (50%)	50%	●
Nitrobenzene	—	●
Oxalic acid	—	●
Ozone (gas)	≤0.5 ppm	●
Paraffin oil	100%	●
Perchloroethylene	—	●
Petroleum	100%	●
Petroleum ether	100%	●

Plastshop

Kemikaali	Pitoisuus	Kestäv.
Phenol, aqueous	ca. 9%	●
Phosphoric acid	50%	●
Potassium hydroxide solution	50%	●
Premium fuel	—	●
Propyl alcohol	—	●
Silicone oil	—	●
Sodium carbonate, aqueous	—	●
Sodium chloride, aqueous	—	●
Sodium hydrogen sulfite	—	●
Sodium hydroxide solution (15%)	15%	●
Sodium hydroxide solution (60%)	60%	●
Sodium nitrate, aqueous	—	●
Sulphuric acid	96%	●
Tetrahydrofuran (THF)	100%	●
Toluene	100%	●
Transformer oil	—	●
Trichloroethylene	100%	●
Vinegar, standard	5-10%	●
Water	—	●
Xylene	—	●