



PVC U 16x5000 mm SDR 13,5 lÃ¶pinÃ¶kyvÃ¶

Artikelnr P2202289

BestÃ¶ndig Delvis bestÃ¶ndig Ej bestÃ¶ndig

Kemikalie	Pitoisuus	Temp.	BestÃ¶ndighet
1,4-Dioxane	100%	20 Å°C	
2-Hydroxypropionic acid (lactic acid)	90%	20 Å°C	
Acetic acid	100%	20 Å°C	
Acetone	100%	20 Å°C	
Ammonia	conc.	20 Å°C	
Ammonium chloride	â€	20 Å°C	
Amyl alcohol	â€	20 Å°C	
Apple juice	â€	20 Å°C	
Benzene	â€	20 Å°C	
Bleaching solution	12.5 cl	20 Å°C	
Boric acid	100%	20 Å°C	
Brake fluid	â€	20 Å°C	
Butyl acetate	â€	20 Å°C	
Calcium chloride	â€	20 Å°C	
Carbon disulphide	100%	20 Å°C	
Carbon tetrachloride	â€	20 Å°C	
Chlorine (gas)	100%	20 Å°C	
Chlorobenzene	100%	20 Å°C	
Chloroform	â€	20 Å°C	
Citric acid	10%	20 Å°C	
Cresol	â€	20 Å°C	
Cyclohexanone	100%	20 Å°C	
Cyclohexene	100%	20 Å°C	
Diesel	â€	20 Å°C	
Diethylene oxide	â€	20 Å°C	
Ethyl acetate	100%	20 Å°C	
Ethyl alcohol (ethanol)	96%	20 Å°C	

Kemikalie	Pitoisuus	Temp.	Beständighet
Ethylene chloride	100%	20 Å°C	
Food oil	â€”	20 Å°C	
Formaldehyde (aqueous)	40%	20 Å°C	
Formic acid	10%	20 Å°C	
Frost protection agent	â€”	20 Å°C	
Fuel (aromatic free)	â€”	20 Å°C	
Fuel oil	â€”	20 Å°C	
Glycerine	100%	20 Å°C	
Glycol	100%	20 Å°C	
Heptane	100%	20 Å°C	
Hydrochloric acid	10%	20 Å°C	
Hydrochloric acid (concentrated)	conc.	20 Å°C	
Hydrofluoric acid	40%	20 Å°C	
Hydrogen peroxide	10%	20 Å°C	
Hydrogen sulfide (aqueous)	â€”	20 Å°C	
Isopropyl alcohol	100%	20 Å°C	
Linseed oil	â€”	20 Å°C	
Mercurochrome	â€”	20 Å°C	
Methyl alcohol (methanol)	100%	20 Å°C	
Methyl ethyl ketone (MEK)	100%	20 Å°C	
Methylene chloride	100%	20 Å°C	
Milk	â€”	20 Å°C	
Mineral oils (aromatic free)	â€”	20 Å°C	
Nitric acid	50%	20 Å°C	
Nitric acid	10%	20 Å°C	
Nitrobenzene	â€”	20 Å°C	
Oxalic acid	â€”	20 Å°C	
Ozone (gas)	â‰‰ 0.5 ppm	20 Å°C	
Paraffin oil	100%	20 Å°C	
Perchloroethylene	â€”	20 Å°C	
Petroleum	100%	20 Å°C	
Petroleum ether	100%	20 Å°C	
Phenol (aqueous)	ca. 9%	20 Å°C	
Phosphoric acid	50%	20 Å°C	
Potassium hydroxide solution	50%	20 Å°C	

Kemikalie	Pitoisuus	Temp.	Beständighet
Premium fuel	â€”	20 Å°C	●
Propyl alcohol	â€”	20 Å°C	●
Pyridine	â€”	20 Å°C	●
Silicone oil	â€”	20 Å°C	●
Sodium carbonate (aqueous)	â€”	20 Å°C	●
Sodium chloride (aqueous)	â€”	20 Å°C	●
Sodium hydrogen sulfite	â€”	20 Å°C	●
Sodium hydroxide solution (caustic soda)	15%	20 Å°C	●
Sodium hydroxide solution (caustic soda)	60%	20 Å°C	●
Sodium nitrate (aqueous)	â€”	20 Å°C	●
Sodium thiosulfate	â€”	20 Å°C	●
Sulphuric acid	96%	20 Å°C	●
Tetrahydrofuran (THF)	100%	20 Å°C	●
Toluene	100%	20 Å°C	●
Transformer oil	â€”	20 Å°C	●
Trichloroethylene	100%	20 Å°C	●
Vinegar (standard)	5 - 10%	20 Å°C	●
Water	â€”	20 Å°C	●
Xylene	â€”	20 Å°C	●