



Rundstång i PET 56x3000 mm natur

Artikelnr P1003641

● Beständig

● Delvis beständig

● Ej beständig

Kemikalie	Koncentration	Temp.	Beständighet
1,4-Dioxan	100	20 Å°C	●
1,4-Dioxan	100	60 Å°C	●
Aceton	100	60 Å°C	●
Aceton	100	20 Å°C	●
Ammoniak	conc.	20 Å°C	●
Ammoniak	conc.	60 Å°C	●
Bensen	â€”	20 Å°C	●
Bensen	â€”	60 Å°C	●
Bensin (premium)	â€”	60 Å°C	●
Bensin (premium)	â€”	20 Å°C	●
Blekningsl��sning	â€”	20 Å°C	●
Bromsv��tska	â€”	20 Å°C	●
Bromsv��tska	â€”	60 Å°C	●
Br��nsle, aromatfritt	â€”	60 Å°C	●
Br��nsle, aromatfritt	â€”	20 Å°C	●
Butylacetat	â€”	20 Å°C	●
Butylacetat	â€”	60 Å°C	●
Citronsyra	10	20 Å°C	●
Citronsyra	10	60 Å°C	●
Diesel	â€”	20 Å°C	●
Diesel	â€”	60 Å°C	●
Dietylenoxid	â€”	20 Å°C	●
Dietylenoxid	â€”	20 Å°C	●
Eldningsolja	â€”	60 Å°C	●
Eldningsolja	â€”	20 Å°C	●
Etylacetat	100	60 Å°C	●
Etylacetat	100	20 Å°C	●

Kemikalie	Koncentration	Temp.	Beständighet
Etylalkohol (etanol)	96%	20 Å°C	●
Etylalkohol (etanol)	96	20 Å°C	●
Etylalkohol (etanol)	96	60 Å°C	●
Etylenklorid	100	20 Å°C	●
Etylenklorid	100	60 Å°C	●
Fenol, vattenl.	ca.9	20 Å°C	●
Fluorvätesyra	40%	20 Å°C	●
Fluorvätesyra	40	60 Å°C	●
Fluorvätesyra	40	20 Å°C	●
Fosforsyra	50	60 Å°C	●
Fosforsyra	50	20 Å°C	●
Frostskyddsmedel	â€”	60 Å°C	●
Frostskyddsmedel	â€”	20 Å°C	●
Glycerin	100	20 Å°C	●
Glycerin	100	60 Å°C	●
Glycerin	100%	20 Å°C	●
Glykol	100	60 Å°C	●
Glykol	100	20 Å°C	●
Heptan	100	20 Å°C	●
Heptan	100	60 Å°C	●
Isopropylalkohol	100	20 Å°C	●
Isopropylalkohol	100%	20 Å°C	●
Isopropylalkohol	100	60 Å°C	●
Kalciumklorid	â€”	20 Å°C	●
Kalciumklorid	â€”	60 Å°C	●
Kaliumhydroxidlösning	50	20 Å°C	●
Kaliumhydroxidlösning	50	60 Å°C	●
Klorbensen	100	60 Å°C	●
Klorbensen	100%	20 Å°C	●
Klorbensen	100	20 Å°C	●
Kloroform	â€”	60 Å°C	●
Kloroform	â€”	20 Å°C	●
Koldisulfid	100	60 Å°C	●
Koldisulfid	100	20 Å°C	●

Kemikalie	Koncentration	Temp.	Best�ndighet
Koltetraklorid	â€”	20 �C	●
Koltetraklorid	â€”	60 �C	●
Koltetraklorid	â€”	20 �C	●
Linolja	â€”	20 �C	●
Linolja	â€”	60 �C	●
Matolja	â€”	60 �C	●
Matolja	â€”	20 �C	●
Matolja	â€”	20 �C	●
Merkurokrom	â€”	20 �C	●
Metylalkohol (metanol)	100	20 �C	●
Metylalkohol (metanol)	100%	20 �C	●
Metylalkohol (metanol)	100	60 �C	●
Metylenklorid	100	60 �C	●
Metylenklorid	100	20 �C	●
Metyletylketon (MEK)	100	20 �C	●
Metyletylketon (MEK)	100	60 �C	●
Mineraloljor, aromatfria	â€”	60 �C	●
Mineraloljor, aromatfria	â€”	20 �C	●
Mj�lk	â€”	20 �C	●
Mj�lk	â€”	60 �C	●
Myrsyra	10	60 �C	●
Myrsyra	10	20 �C	●
Natriumhydroxid�sning (natronlut)	60	60 �C	●
Natriumhydroxid�sning (natronlut)	15	60 �C	●
Natriumhydroxid�sning (natronlut)	60	20 �C	●
Natriumhydroxid�sning (natronlut)	15	20 �C	●
Natriumkarbonat, vattenl.	â€”	60 �C	●
Natriumkarbonat, vattenl.	â€”	20 �C	●
Natriumklorid, vattenl.	â€”	20 �C	●
Natriumklorid, vattenl.	â€”	60 �C	●
Natriumnitrat, vattenl.	â€”	20 �C	●
Natriumtiosulfat	â€”	20 �C	●
Natriumv�tesulfid	â€”	20 �C	●
Natriumv�tesulfid	â€”	20 �C	●

Kemikalie	Koncentration	Temp.	Best�ndighet
Natriumv��tesulfid	���	60 ��C	��
Paraffinolja	100	20 ��C	��
Paraffinolja	100	60 ��C	��
Perkloretylen	���	60 ��C	��
Perkloretylen	���	20 ��C	��
Petroleum	100	20 ��C	��
Petroleum	100%	20 ��C	��
Petroleumeter	100	20 ��C	��
Petroleumeter	100	60 ��C	��
Petroleumeter	100%	20 ��C	��
Propylalkohol	���	20 ��C	��
Propylalkohol	���	60 ��C	��
Salpetersyra	10	60 ��C	��
Salpetersyra	10%	20 ��C	��
Salpetersyra	10	20 ��C	��
Salpetersyra	50	20 ��C	��
Salpetersyra	50	60 ��C	��
Saltsyra	conc.	60 ��C	��
Saltsyra	10	60 ��C	��
Saltsyra	10	20 ��C	��
Saltsyra	conc.	20 ��C	��
Saltsyra (konc.)	conc.	20 ��C	��
Silikonolja	���	20 ��C	��
Silikonolja	���	60 ��C	��
Svavelsyra	96	20 ��C	��
Svavelsyra	96	60 ��C	��
Tetrahydrofuran (THF)	100	20 ��C	��
Tetrahydrofuran (THF)	100	60 ��C	��
Toluen	100	20 ��C	��
Toluen	100	60 ��C	��
Toluen	100%	20 ��C	��
Transformatorolja	���	20 ��C	��
Transformatorolja	���	60 ��C	��
Trikloret�n	100	20 ��C	��
Trikloret�n	100	60 ��C	��

